

# A-TSI-1214-12 Cut Sheet



igus iglide series plain bearing, type T500 polymer, 3/4in inside diameter, 7/8in outside diameter, 3/4in overall length. Package of 2. For use with 3/4in diameter drylin R series shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A-TSI-1214-12>

## Technical Specifications

Brand	igus
Item	Plain bearing
Series	Iglide
Bearing Material	Type T500 polymer
Bearing Inside Diameter	3/4in
Bearing Outside Diameter	7/8in
Overall Length	3/4in
Flanged	No
Quantity per Pack	2
For Use With	3/4in diameter drylin R series shafts
Application	Chemical resistant, high temperatures

## Agency Approvals

CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A-TSI-1214-12.pdf>  
See store item page for other formats.