

A060604 Cut Sheet



Wiegmann enclosure, NEMA 1, 6 x 6 x 4in (HxWxD), wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, single-door, integral snap-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A060604>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	Yes
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Carbon steel
Vented	No	Color	ANSI 61 gray
NEMA Rating	1	Finish	Powder coat
Nominal Enclosure Dimensions	6 x 6 x 4in (HxWxD)	Cover Type	Single-door
Enclosure Height	6.37in	Hinge Type	Clamp-style hinges
Enclosure Width	6.37in	Number of Hinges Per Door	2
Enclosure Depth	4.38in	Latch Type	Integral snap-tight latch
Mounting	Wall	Shelf	No
Integral Mounting Feet	No	Padlockable	No
Integral Mounting Flange	No	Keylocking	No

Agency Approvals

UL Listed File #	E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A060604.pdf>
See store item page for other formats.