

A07010SP Cut Sheet

NITRA pneumatic cylinder, non-repairable, 7/16in bore, 3/16in rod diameter, 1in stroke, single acting, rear pivot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A07010SP>



Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Non-repairable
Bore Diameter	7/16in
Stroke	1in
Port Size	#10-32 female UNF
Mounting	Rear pivot

Action Type	Single acting
Action	Spring return
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Stainless steel
Rod Diameter	3/16in
Rod Thread Size	#10-32

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A07010SP.pdf>
See store item page for other formats.