

# A07015SP Cut Sheet

NITRA pneumatic cylinder, non-repairable, 7/16in bore, 3/16in rod diameter, 1-1/2in stroke, single acting, rear pivot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A07015SP>

## Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Non-repairable
Bore Diameter	7/16in
Stroke	1-1/2in
Port Size	#10-32 female UNF
Mounting	Rear pivot

Action Type	Single acting
Action	Spring return
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Stainless steel
Rod Diameter	3/16in
Rod Thread Size	#10-32

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A07015SP.pdf>  
See store item page for other formats.