

A09010SD Cut Sheet



NITRA pneumatic cylinder, non-repairable, 9/16in bore, 3/16in rod diameter, 1in stroke, single acting, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A09010SD>

Technical Specifications

| | |
|----------------------|-------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | Non-repairable |
| Bore Diameter | 9/16in |
| Stroke | 1in |
| Port Size | #10-32 female UNF |
| Mounting | Double end |

| | |
|-------------------------|-----------------|
| Action Type | Single acting |
| Action | Spring return |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Stainless steel |
| Rod Diameter | 3/16in |
| Rod Thread Size | #10-32 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A09010SD.pdf>
See store item page for other formats.