

A104265-1 Cut Sheet



LUTZE continuous flexing Profibus cable, shielded, 1 twisted pair, 24 AWG, 19-stranded, bare copper, special polyolefin conductor insulation material, PUR jacket, purple, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A104265-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Material	Special polyolefin
Item	Cable	Conductor Insulation Color	Red and green
Protocol	Fieldbus	Shielding	Shielded
Wire/Cable Type	Profibus	Jacket Material	PUR
UL Wire/Cable Type	CMX and AWM	Jacket Color	Purple
Applicable Standards	NFPA 79, UL 1581 and UL 21198	Nominal Overall Cable Diameter	0.315in
Application	Data	Bulk Length	Cut to length
Flexibility	Continuous flexing	Package Type	1 to 75ft = Coil, 76 to 390ft = 14 x 7in Reel, 391 to 560ft = 14 x 10in Reel, 561 to 870ft = 16 x 10in Reel, 871 to 1000ft = 18 x 10in Reel
Voltage Rating	300V		
Conductors	1 twisted pair		
Conductor Size	24 AWG		
Conductor Stranding	19-stranded		
Conductor Material	Bare copper		

Agency Approvals

UL Listed File #	E319350
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document