

A104293-1 Cut Sheet



LUTZE Profibus cable, shielded, 1 twisted pair, 22 AWG, solid, bare copper, special polyolefin conductor insulation material, PVC jacket, purple, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A104293-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Material	Special polyolefin
Item	Cable	Conductor Insulation Color	Red and green
Protocol	Fieldbus	Shielding	Shielded
Wire/Cable Type	Profibus	Jacket Material	PVC
UL Wire/Cable Type	CMG and AWM	Jacket Color	Purple
Applicable Standards	NFPA 79, UL 20201 and UL 1685	Nominal Overall Cable Diameter	0.307in
Application	Data	Bulk Length	Cut to length
Flexibility	Semi-flexible		1 to 99ft = Coil, 100 to 402ft = 14 x 7in Reel, 403 to 582ft = 14 x 10in Reel, 583 to 905ft = 16 x 10in Reel, 906 to 1000ft = 18 x 10in Reel
Voltage Rating	300V	Package Type	
Conductors	1 twisted pair		
Conductor Size	22 AWG		
Conductor Stranding	Solid		
Conductor Material	Bare copper		

Agency Approvals

UL Listed File #	E319350
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document