

A104338-1 Cut Sheet



LUTZE flexible Cat6a industrial Ethernet cable, shielded, 4 twisted pairs, 26 AWG, 7-stranded, bare copper, special polyolefin conductor insulation material, PVC jacket, green, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A104338-1>

Technical Specifications

Brand	LUTZE
Item	Cable
Protocol	Ethernet
Wire/Cable Type	Cat6a industrial Ethernet
UL Wire/Cable Type	CMG
Applicable Standards	NFPA 79 and UL 1685
Application	Data
Flexibility	Flexible
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	26 AWG
Conductor Stranding	7-stranded
Conductor Material	Bare copper
Conductor Insulation Material	Special polyolefin

Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Green
Nominal Overall Cable Diameter	0.252in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 615ft = 14 x 7in Reel• 616 to 875ft = 14 x 10in Reel• 876 to 1000ft = 16 x 10in Reel

Agency Approvals

UL Listed File #	E319350
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document