

A104397-1 Cut Sheet



LUTZE flexible Cat6a industrial Ethernet Profinet cable, shielded, 4 twisted pairs, 22 AWG, solid, bare copper, special polyolefin conductor insulation material, PVC jacket, green, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A104397-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Color	Pair 1: blue, white/blue, Pair 2: orange, white/orange, Pair 3: green, white/green and Pair 4: brown, white/brown
Item	Cable	Shielding	Shielded
Protocol	Ethernet and fieldbus	Jacket Material	PVC
Wire/Cable Type	Cat6a industrial Ethernet and Profinet	Jacket Color	Green
UL Wire/Cable Type	CMG, PLTC and AWM	Nominal Overall Cable Diameter	0.378in
Applicable Standards	NFPA 79, UL 2570 and UL 1685	Bulk Length	Cut to length
Application	Data	Package Type	1 to 75ft = Coil, 76 to 270ft = 14 x 7in Reel, 271 to 390ft = 14 x 10in Reel, 391 to 600ft = 16 x 10in Reel, 601 to 850ft = 18 x 10in Reel, 851 to 1000ft = 18 x 13in Reel
Flexibility	Flexible		
Voltage Rating	600V		
Conductors	4 twisted pairs		
Conductor Size	22 AWG		
Conductor Stranding	Solid		
Conductor Material	Bare copper		
Conductor Insulation Material	Special polyolefin		

Agency Approvals

UL Listed File #	E331083
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document