

# A1061004-1 Cut Sheet



LUTZE DRIVEFLEX VFD cable, 4 conductors (includes ground), 10 AWG, 105-stranded, tinned copper, XLPE conductor insulation material, XHHW-2 jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1061004-1>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Cable
<b>Series</b>	DRIVEFLEX
<b>Wire/Cable Type</b>	VFD
<b>UL Wire/Cable Type</b>	TC-ER-JP and WTTTC
<b>Applicable Standards</b>	UL 1277
<b>Application</b>	Drive and motor
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	600V (Type TC-ER-JP), 1000V (Type WTTTC, Flexible Motor Supply Cable)
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	10 AWG
<b>Conductor Stranding</b>	105-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	XLPE

<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground
<b>Shielding</b>	Overall foil and braid shielded
<b>Jacket Material</b>	XHHW-2
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.65in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 50ft = Coil, 51 to 90ft = Coil, 91 to 120ft = 14 x 7in Reel, 121 to 200ft = 14 x 10in Reel, 201 to 280ft = 16 x 10in Reel, 281 to 360ft = 18 x 10in Reel, 361 to 780ft = 18 x 13in Reel, 781 to 1290ft = 24 x 17in Wooden Reel, 1291 to 2147483647 = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E352875
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>