

A12015SP Cut Sheet



NITRA pneumatic cylinder, non-repairable, 3/4in bore, 1/4in rod diameter, 1 1/2in stroke, single acting, rear pivot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A12015SP>

Technical Specifications

| | |
|------------------|------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air |
| Cylinder Type | Non-repairable |
| Bore Diameter | 3/4in |
| Stroke | 1 1/2in |
| Port Size | 1/8in female NPT |
| Mounting | Rear pivot |
| Action Type | Single acting |
| Action | Spring return |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Steel |
| Rod Diameter | 1/4in |
| Rod Thread Size | 1/4-28 |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |