

# A12060DP-M Cut Sheet



NITRA pneumatic cylinder, non-repairable, 3/4in bore, 1/4in rod diameter, 6in stroke, double acting, magnetic piston, rear pivot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A12060DP-M>

## Technical Specifications

|               |                  |
|---------------|------------------|
| Brand         | NITRA            |
| Item          | Cylinder         |
| Working Fluid | Air or inert gas |
| Cylinder Type | Non-repairable   |
| Bore Diameter | 3/4in            |
| Stroke        | 6in              |
| Port Size     | 1/8in female NPT |
| Mounting      | Rear pivot       |

|                  |                 |
|------------------|-----------------|
| Action Type      | Double acting   |
| Magnetic Piston  | Magnetic piston |
| Body Material    | Stainless steel |
| End Cap Material | Aluminum        |
| Rod Material     | Stainless steel |
| Rod Diameter     | 1/4in           |
| Rod Thread Size  | 1/4-28          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A12060DP-M.pdf>  
See store item page for other formats.