

A14030DD-M Cut Sheet



NITRA pneumatic cylinder, non-repairable, 7/8in bore, 1/4in rod diameter, 3in stroke, double acting, magnetic piston, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A14030DD-M>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	Non-repairable
Bore Diameter	7/8in
Stroke	3in
Port Size	1/8in female NPT
Mounting	Double end
Action Type	Double acting
Magnetic Piston	Magnetic piston
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Stainless steel
Rod Diameter	1/4in
Rod Thread Size	1/4-28

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document