


A1481804-1 Cut Sheet



LUTZE SUPERFLEX continuous flexing control cable, unshielded, 4 conductors (includes ground), 18 AWG (1.0mm²), bare copper, TPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1481804-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Color	Black with white numbers and green/yellow ground
Item	Cable	Shielding	Unshielded
Series	SUPERFLEX	Jacket Material	PVC
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	AWM	Nominal Overall Cable Diameter	0.264in
Applicable Standards	UL 2586	Bulk Length	Cut to length
Application	Automation	Package Type	1 to 99ft = Coil, 100 to 555ft = 14 x 7in Reel, 556 to 780ft = 14 x 10in Reel, 781 to 1240ft = 16 x 10in Reel, 1241 to 1735ft = 18 x 10in Reel, 1736 to 2255ft = 18 x 13in Reel, 2256 to 3280ft = 24 x 17in Wooden Reel
Flexibility	Continuous flexing		
Voltage Rating	600V rated (UL)		
Conductors	4 conductors (includes ground)		
Conductor Size	18 AWG (1.0mm ²)		
Conductor Stranding	56-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	TPE		

Agency Approvals

UL Listed File #	E197090
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document