

A1482007-1 Cut Sheet



LUTZE SUPERFLEX continuous flexing control cable, unshielded, 7 conductors (includes ground), 21 AWG (0.50mm²), bare copper, TPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1482007-1>

Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | LUTZE |
| Item | Cable |
| Series | SUPERFLEX |
| Wire/Cable Type | Control |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 2586 |
| Application | Automation |
| Flexibility | Continuous flexing |
| Voltage Rating | 600V rated (UL) |
| Conductors | 7 conductors (includes ground) |
| Conductor Size | 21 AWG (0.50mm ²) |
| Conductor Stranding | 28-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | TPE |

| | |
|---------------------------------------|--|
| Conductor Insulation Color | Black with white numbers and green/yellow ground |
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | Gray |
| Nominal Overall Cable Diameter | 0.283in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 485ft = 14 x 7in Reel• 486 to 695ft = 14 x 10in Reel• 696 to 1065ft = 16 x 10in Reel• 1066 to 1490ft = 18 x 10in Reel• 1491 to 1940ft = 18 x 13in Reel• 1941 to 3280ft = 24 x 17in Wooden Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E197090 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |