

# A1492007-1 Cut Sheet



LUTZE SUPERFLEX continuous flexing control cable, shielded, 7 conductors (includes ground), 21 AWG (0.50mm<sup>2</sup>), bare copper, TPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A1492007-1>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Cable
<b>Series</b>	SUPERFLEX
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 2586
<b>Application</b>	Automation
<b>Flexibility</b>	Continuous flexing
<b>Voltage Rating</b>	600V rated (UL)
<b>Conductors</b>	7 conductors (includes ground)
<b>Conductor Size</b>	21 AWG (0.50mm <sup>2</sup> )
<b>Conductor Stranding</b>	28-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	TPE

<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground
<b>Shielding</b>	Shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.354in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 75ft = Coil, 76 to 310ft = 14 x 7in Reel, 311 to 445ft = 14 x 10in Reel, 446 to 680ft = 16 x 10in Reel, 681 to 955ft = 18 x 10in Reel, 956 to 1240ft = 18 x 13in Reel, 1241 to 2770ft = 24 x 17in Wooden Reel, 2771 to 3280ft = 30 x 17in Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E197090
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes with Exemptions (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>