

A151506 Cut Sheet



Wiegmann enclosure, NEMA 1, 15 x 15 x 6in (HxWxD), wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, single-door, integral snap-tight latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A151506>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
NEMA Rating	1
Nominal Enclosure Dimensions	15 x 15 x 6in (HxWxD)
Enclosure Height	15.25in
Enclosure Width	15.25in
Enclosure Depth	6.38in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Clamp-style hinges
Number of Hinges Per Door	2
Latch Type	Integral snap-tight latch
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document