

A17005DN Cut Sheet

NITRA pneumatic cylinder, non-repairable, 1-1/16in bore, 5/16in rod diameter, 1/2in stroke, double acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A17005DN>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	Non-repairable
Bore Diameter	1-1/16in
Stroke	1/2in
Port Size	1/8in female NPT
Mounting	Front nose
Action Type	Double acting
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Steel
Rod Diameter	5/16in
Rod Thread Size	5/16-24

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document