

# A20030DD-M Cut Sheet

NITRA pneumatic cylinder, non-repairable, 1-1/4in bore, 7/16in rod diameter, 3in stroke, double acting, magnetic piston, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A20030DD-M>



## Technical Specifications

|                         |                  |
|-------------------------|------------------|
| <b>Brand</b>            | NITRA            |
| <b>Item</b>             | Cylinder         |
| <b>Working Fluid</b>    | Air              |
| <b>Cylinder Type</b>    | Non-repairable   |
| <b>Bore Diameter</b>    | 1-1/4in          |
| <b>Stroke</b>           | 3in              |
| <b>Port Size</b>        | 1/8in female NPT |
| <b>Mounting</b>         | Double end       |
| <b>Action Type</b>      | Double acting    |
| <b>Magnetic Piston</b>  | Magnetic piston  |
| <b>Body Material</b>    | Stainless steel  |
| <b>End Cap Material</b> | Aluminum         |
| <b>Rod Material</b>     | Stainless steel  |
| <b>Rod Diameter</b>     | 7/16in           |
| <b>Rod Thread Size</b>  | 7/16-20          |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |