

A20030SN Cut Sheet

NITRA pneumatic cylinder, non-repairable, 1-1/4in bore, 7/16in rod diameter, 3in stroke, single acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A20030SN>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	Non-repairable
Bore Diameter	1-1/4in
Stroke	3in
Port Size	1/8in female NPT
Mounting	Front nose
Action Type	Single acting
Action	Spring return
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Steel
Rod Diameter	7/16in
Rod Thread Size	7/16-20

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document