

A24-L050-SPBO-1000 Cut Sheet



Sung-II Machinery timing pulley, aluminum, 3/8in L pitch, 24 tooth, 2.865in pitch diameter, 1in bore, no hub with flanges. For use with 1/2in wide belt. QD bushing included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A24-L050-SPBO-1000>

Technical Specifications

| | |
|------------------------|---------------------|
| Brand | Sung-II Machinery |
| Item | Timing pulley |
| Material | Aluminum |
| Pitch | 3/8in L |
| Number of Teeth | 24 |
| Pitch Diameter | 2.865in |
| Bore Diameter | 1in |
| Pulley Type | No hub with flanges |
| Mounting Type | QD style bushing |
| For Use With | 1/2in wide belt |
| Includes | QD bushing |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | Not Applicable |
| UL Recognized File # | Not Applicable |
| UL Hazardous File # | Not Applicable |
| CE | None |
| CSA File # | Not Applicable |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/A24-L050-SPBO-1000.pdf>
See store item page for other formats.