

# A24030SN Cut Sheet



NITRA pneumatic cylinder, non-repairable, 1-1/2in bore, 7/16in rod diameter, 3in stroke, single acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A24030SN>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Cylinder
<b>Working Fluid</b>	Air or inert gas
<b>Cylinder Type</b>	Non-repairable
<b>Bore Diameter</b>	1-1/2in
<b>Stroke</b>	3in
<b>Port Size</b>	1/8in female NPT
<b>Mounting</b>	Front nose

<b>Action Type</b>	Single acting
<b>Action</b>	Spring return
<b>Body Material</b>	Stainless steel
<b>End Cap Material</b>	Aluminum
<b>Rod Material</b>	Steel
<b>Rod Diameter</b>	7/16in
<b>Rod Thread Size</b>	7/16-20

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A24030SN.pdf>  
See store item page for other formats.