

A24050DN Cut Sheet



NITRA pneumatic cylinder, non-repairable, 1-1/2in bore, 7/16in rod diameter, 5in stroke, double acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A24050DN>

Technical Specifications

| | |
|------------------|------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | Non-repairable |
| Bore Diameter | 1-1/2in |
| Stroke | 5in |
| Port Size | 1/8in female NPT |
| Mounting | Front nose |
| Action Type | Double acting |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Steel |
| Rod Diameter | 7/16in |
| Rod Thread Size | 7/16-20 |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A24050DN.pdf>
See store item page for other formats.