

# A24050DP Cut Sheet

NITRA pneumatic cylinder, non-repairable, 1-1/2in bore, 7/16in rod diameter, 5in stroke, double acting, rear pivot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A24050DP>

## Technical Specifications

|                  |                  |
|------------------|------------------|
| Brand            | NITRA            |
| Item             | Cylinder         |
| Working Fluid    | Air or inert gas |
| Cylinder Type    | Non-repairable   |
| Bore Diameter    | 1-1/2in          |
| Stroke           | 5in              |
| Port Size        | 1/8in female NPT |
| Mounting         | Rear pivot       |
| Action Type      | Double acting    |
| Body Material    | Stainless steel  |
| End Cap Material | Aluminum         |
| Rod Material     | Steel            |
| Rod Diameter     | 7/16in           |
| Rod Thread Size  | 7/16-20          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A24050DP.pdf>  
See store item page for other formats.