


A3031615-1 Cut Sheet



LUTZE ELECTRONIC flexible control and signal cable, unshielded, 15 conductors, 16 AWG, 26-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3031615-1>

Technical Specifications

Brand	LUTZE	Shielding	Unshielded
Item	Cable	Jacket Material	PVC
Series	ELECTRONIC	Jacket Color	Gray
Wire/Cable Type	Control and signal	Nominal Overall Cable Diameter	0.532in
UL Wire/Cable Type	PLTC, AWM and CM	Bulk Length	Cut to length
Applicable Standards	UL 2464	Package Type <ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 140ft = 14 x 7in Reel• 141 to 195ft = 14 x 10in Reel• 196 to 300ft = 16 x 10in Reel• 301 to 420ft = 18 x 10in Reel• 421 to 550ft = 18 x 13in Reel• 551 to 1225ft = 24 x 17in Wooden Reel• 1226 to 1965ft = 30 x 17in Wooden Reel• 1966 to 2500ft = Large Wooden Reel	
Application	General purpose and food and beverage		
Flexibility	Flexible		
Voltage Rating	300V		
Conductors	15 conductors		
Conductor Size	16 AWG		
Conductor Stranding	26-stranded		
Conductor Material	Tinned copper		
Conductor Insulation Material	PVC		
Conductor Insulation Color	Black, red, white, green, orange, blue, brown, yellow, violet, gray, pink, tan, red/green, red/yellow and red/black		

Agency Approvals

UL Listed File #	E331083
CE	View CE declarations
CSA File #	LL41103
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document