

# A3081625-1 Cut Sheet



LUTZE Silflex flexible control cable, unshielded, 25 conductors (includes ground), 16 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3081625-1>

## Technical Specifications

<b>Brand</b>	LUTZE	<b>Shielding</b>	Unshielded
<b>Item</b>	Cable	<b>Jacket Material</b>	PVC
<b>Series</b>	Silflex	<b>Jacket Color</b>	Gray
<b>Wire/Cable Type</b>	Control	<b>Nominal Overall Cable Diameter</b>	0.748in
<b>UL Wire/Cable Type</b>	TC, TC-ER, WTTC and MTW	<b>Bulk Length</b>	Cut to length
<b>Application</b>	General purpose	<b>Package Type</b>	1 to 30ft = Coil, 31 to 70ft = 14 x 7in Reel, 71 to 100ft = 14 x 10in Reel, 101 to 155ft = 16 x 10in Reel, 156 to 215ft = 18 x 10in Reel, 216 to 275ft = 18 x 13in Reel, 276 to 620ft = 24 x 17in Wooden Reel, 621 to 995ft = 30 x 17in Wooden Reel, 996 to MAX = Large Wooden Reel
<b>Flexibility</b>	Flexible		
<b>Voltage Rating</b>	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)		
<b>Conductors</b>	25 conductors (includes ground)		
<b>Conductor Size</b>	16 AWG		
<b>Conductor Stranding</b>	26-stranded		
<b>Conductor Material</b>	Bare copper		
<b>Conductor Insulation Material</b>	PVC/Nylon		
<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground		

## Agency Approvals

<b>UL Listed File #</b>	E324630
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>