

A3081825-1 Cut Sheet



LUTZE Silflex flexible control cable, unshielded, 25 conductors (includes ground), 18 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3081825-1>

Technical Specifications

Brand	LUTZE	Shielding	Unshielded
Item	Cable	Jacket Material	PVC
Series	Silflex	Jacket Color	Gray
Wire/Cable Type	Control	Nominal Overall Cable Diameter	0.677in
UL Wire/Cable Type	TC, TC-ER, WTTC and MTW	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 50ft = Coil, 51 to 85ft = 14 x 7in Reel, 86 to 120ft = 14 x 10in Reel, 121 to 185ft = 16 x 10in Reel, 186 to 260ft = 18 x 10in Reel, 261 to 340ft = 18 x 13in Reel, 341 to 760ft = 24 x 17in Wooden Reel, 761 to 1210ft = 30 x 17in Wooden Reel, 1211 to MAX = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)		
Conductors	25 conductors (includes ground)		
Conductor Size	18 AWG		
Conductor Stranding	19-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC/Nylon		
Conductor Insulation Color	Black with white numbers and green/yellow ground		

Agency Approvals

UL Listed File #	E324630
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement