

A3091625-1 Cut Sheet



LUTZE Silflex flexible control cable, shielded, 25 conductors (includes ground), 16 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3091625-1>

Technical Specifications

Brand	LUTZE	Shielding	Shielded
Item	Cable	Jacket Material	PVC
Series	Silflex	Jacket Color	Gray
Wire/Cable Type	Control	Nominal Overall Cable Diameter	0.757in
UL Wire/Cable Type	TC, TC-ER, WTTC and MTW	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 30ft = Coil, 31 to 70ft = 14 x 7in Reel, 71 to 95ft = 14 x 10in Reel, 96 to 150ft = 16 x 10in Reel, 151 to 210ft = 18 x 10in Reel, 211 to 270ft = 18 x 13in Reel, 271 to 605ft = 24 x 17in Wooden Reel, 606 to 970ft = 30 x 17in Wooden Reel, 971 to MAX = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)		
Conductors	25 conductors (includes ground)		
Conductor Size	16 AWG		
Conductor Stranding	26-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC/Nylon		
Conductor Insulation Color	Black with white numbers and green/yellow ground		

Agency Approvals

UL Listed File #	E324630
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement