


A3161204-1 Cut Sheet



LUTZE Silflex flexible servo cable, shielded, 4 conductors (includes ground), 12 AWG, bare copper, PVC/Nylon conductor insulation material, brown, black, blue and green/yellow ground, TPE jacket, orange, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3161204-1>

Technical Specifications

| | |
|--------------------------------------|---|
| Brand | LUTZE |
| Item | Cable |
| Series | Silflex |
| Wire/Cable Type | Servo |
| UL Wire/Cable Type | TC-ER and WTTC |
| Applicable Standards | UL 2277 |
| Application | Drive and motor |
| Flexibility | Flexible |
| Voltage Rating | 600V (Type TC-ER), 1000V (Type WTTC, Flexible Motor Supply Cable) |
| Conductors | 4 conductors (includes ground) |
| Conductor Size | 12 AWG |
| Conductor Stranding | 65-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | PVC/Nylon |

| | |
|---------------------------------------|---|
| Conductor Insulation Color | Brown, black, blue and green/yellow ground |
| Shielding | Tinned copper braid |
| Jacket Material | TPE |
| Jacket Color | Orange |
| Nominal Overall Cable Diameter | 0.51in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 150ft = 14 x 7in Reel• 151 to 215ft = 14 x 10in Reel• 216 to 330ft = 16 x 10in Reel• 331 to 460ft = 18 x 10in Reel• 461 to 595ft = 18 x 13in Reel• 596 to 1335ft = 24 x 17in Wooden Reel• 1336 to 2135ft = 30 x 17in Wooden Reel• 2136 to 2500ft = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E352875 |
| UL Recognized File # | E197090 |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |