


# A3161404-1 Cut Sheet



LUTZE Silflex flexible servo cable, shielded, 4 conductors (includes ground), 14 AWG, bare copper, PVC/Nylon conductor insulation material, brown, black, blue and green/yellow ground, TPE jacket, orange, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3161404-1>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Cable
<b>Series</b>	Silflex
<b>Wire/Cable Type</b>	Servo
<b>UL Wire/Cable Type</b>	TC-ER and WTTC
<b>Applicable Standards</b>	UL 2277
<b>Application</b>	Drive and motor
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V (Type TC-ER), 1000V (Type WTTC, Flexible Motor Supply Cable)
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	14 AWG
<b>Conductor Stranding</b>	41-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	PVC/Nylon

<b>Conductor Insulation Color</b>	Brown, black, blue and green/yellow ground
<b>Shielding</b>	Tinned copper braid
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Orange
<b>Nominal Overall Cable Diameter</b>	0.455in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 20 to 50ft = Coil</li><li>• 51 to 190ft = 14 x 7in Reel</li><li>• 191 to 270ft = 14 x 10in Reel</li><li>• 271 to 415ft = 16 x 10in Reel</li><li>• 416 to 575ft = 18 x 10in Reel</li><li>• 576 to 750ft = 18 x 13in Reel</li><li>• 751 to 1675ft = 24 x 17in Wooden Reel</li><li>• 1676 to 2500ft = 30 x 17in Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E352875
<b>UL Recognized File #</b>	E197090
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>