


A3170804-1 Cut Sheet



LUTZE Silflex flexible servo cable, shielded, 4 conductors (includes ground), 8 AWG, bare copper, (1) shielded 18 AWG twisted pair, PVC/Nylon conductor insulation material, brown, black, blue and green/yellow ground, TPE jacket, orange, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3170804-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Color	Brown, black, blue and green/yellow ground
Item	Cable	Shielding	Tinned copper braid
Series	Silflex	Jacket Material	TPE
Wire/Cable Type	Servo	Jacket Color	Orange
UL Wire/Cable Type	TC-ER and WTTC	Nominal Overall Cable Diameter	0.89in
Applicable Standards	UL 2277	Bulk Length	Cut to length
Application	Drive and motor	Package Type	<ul style="list-style-type: none">• 20 to 30ft = Coil• 31 to 50ft = 14 x 7in Reel• 51 to 70ft = 14 x 10in Reel• 71 to 110ft = 16 x 10in Reel• 111 to 150ft = 18 x 10in Reel• 151 to 195ft = 18 x 13in Reel• 196 to 440ft = 24 x 17in Wooden Reel• 441 to 700ft = 30 x 17in Wooden Reel• 701 to 1000ft = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V (Type TC-ER), 1000V (Type WTTC, Flexible Motor Supply Cable)		
Conductors	4 conductors (includes ground)		
Conductor Size	8 AWG		
Conductor Stranding	168-stranded		
Conductor Material	Bare copper		
Auxiliary Conductors	(1) shielded 18 AWG twisted pair		
Conductor Insulation Material	PVC/Nylon		

Agency Approvals

UL Listed File #	E352875
UL Recognized File #	E197090
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement