

# A32020SN Cut Sheet



NITRA pneumatic cylinder, non-repairable, 2in bore, 5/8in rod diameter, 2in stroke, single acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A32020SN>

## Technical Specifications

|               |                  |
|---------------|------------------|
| Brand         | NITRA            |
| Item          | Cylinder         |
| Working Fluid | Air or inert gas |
| Cylinder Type | Non-repairable   |
| Bore Diameter | 2in              |
| Stroke        | 2in              |
| Port Size     | 1/4in female NPT |
| Mounting      | Front nose       |

|                  |                 |
|------------------|-----------------|
| Action Type      | Single acting   |
| Action           | Spring return   |
| Body Material    | Stainless steel |
| End Cap Material | Aluminum        |
| Rod Material     | Steel           |
| Rod Diameter     | 5/8in           |
| Rod Thread Size  | 1/2-20          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/A32020SN.pdf>  
See store item page for other formats.