

A32040DN Cut Sheet

NITRA pneumatic cylinder, non-repairable, 2in bore, 5/8in rod diameter, 4in stroke, double acting, front nose mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A32040DN>

Technical Specifications

| | |
|------------------|------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | Non-repairable |
| Bore Diameter | 2in |
| Stroke | 4in |
| Port Size | 1/4in female NPT |
| Mounting | Front nose |
| Action Type | Double acting |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Steel |
| Rod Diameter | 5/8in |
| Rod Thread Size | 1/2-20 |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A32040DN.pdf>
See store item page for other formats.