

A32160DD Cut Sheet

NITRA pneumatic cylinder, non-repairable, 2in bore, 5/8in rod diameter, 16in stroke, double acting, double end mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A32160DD>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Non-repairable
Bore Diameter	2in
Stroke	16in
Port Size	1/4in female NPT
Mounting	Double end
Action Type	Double acting
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Steel
Rod Diameter	5/8in
Rod Thread Size	1/2-20

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/A32160DD.pdf>
See store item page for other formats.