

A3251803-1 Cut Sheet



LUTZE Silflex flexible control cable, unshielded, 3 conductors (includes ground), 18 AWG, bare copper, PVC/Nylon conductor insulation material, blue with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A3251803-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Material	PVC/Nylon
Item	Cable	Conductor Insulation Color	Blue with white numbers and green/yellow ground
Series	Silflex	Shielding	Unshielded
Wire/Cable Type	Control	Jacket Material	PVC
UL Wire/Cable Type	TC-ER and MTW	Jacket Color	Gray
Application	24VDC (NFPA 79)	Nominal Overall Cable Diameter	0.288in
Flexibility	Flexible	Bulk Length	Cut to length
Voltage Rating	600V (Types TC-ER, MTW)	Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 470ft = 14 x 7in Reel• 471 to 670ft = 14 x 10in Reel• 671 to 1000ft = 16 x 10in Reel
Conductors	3 conductors (includes ground)		
Conductor Size	18 AWG		
Conductor Stranding	19-stranded		
Conductor Material	Bare copper		

Agency Approvals

UL Listed File #	E197091
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	LL41103
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement