

A40-L100-SPBO-1000 Cut Sheet



Sung-II Machinery timing pulley, aluminum, 3/8in L pitch, 40 tooth, 4.775in pitch diameter, 1in bore, no hub with flanges. For use with 1in wide belt. QD bushing included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A40-L100-SPBO-1000>

Technical Specifications

| | |
|------------------------|---------------------|
| Brand | Sung-II Machinery |
| Item | Timing pulley |
| Material | Aluminum |
| Pitch | 3/8in L |
| Number of Teeth | 40 |
| Pitch Diameter | 4.775in |
| Bore Diameter | 1in |
| Pulley Type | No hub with flanges |
| Mounting Type | QD style bushing |
| For Use With | 1in wide belt |
| Includes | QD bushing |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | Not Applicable |
| UL Recognized File # | Not Applicable |
| UL Hazardous File # | Not Applicable |
| CE | None |
| CSA File # | Not Applicable |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/A40-L100-SPBO-1000.pdf>
See store item page for other formats.