

# A4060804-1 Cut Sheet



LUTZE MOTIONFLEX continuous flexing VFD cable, shielded, 4 conductors (includes ground), 8 AWG, 336-stranded, tinned copper, XLPE conductor insulation material, XHHW-2 jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A4060804-1>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Cable
<b>Series</b>	MOTIONFLEX
<b>Wire/Cable Type</b>	VFD
<b>UL Wire/Cable Type</b>	TC-ER and WTTC
<b>Applicable Standards</b>	UL 1277
<b>Application</b>	Drive and motor
<b>Flexibility</b>	Continuous flexing
<b>Voltage Rating</b>	600V (Type TC-ER), 1000V (Type WTTC, Flexible Motor Supply Cable)
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	8 AWG
<b>Conductor Stranding</b>	336-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	XLPE

<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground
<b>Shielding</b>	Tinned copper braid
<b>Jacket Material</b>	XHHW-2
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.775in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 50ft = Coil, 51 to 65ft = 14 x 7in Reel, 66 to 95ft = 14 x 10in Reel, 96 to 140ft = 16 x 10in Reel, 141 to 200ft = 18 x 10in Reel, 201 to 260ft = 18 x 13in Reel, 261 to 580ft = 24 x 17in Wooden Reel, 581 to 925ft = 30 x 17in Wooden Reel, 926 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E352875
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>