

A44-8M30-SPBO-1125 Cut Sheet



Sung-II Machinery timing pulley, aluminum, 8mm 8M pitch, 44 tooth, 4.411in pitch diameter, 1-1/8in bore, no hub with flanges. For use with 30mm wide belt. QD bushing included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A44-8M30-SPBO-1125>

Technical Specifications

Brand	Sung-II Machinery
Item	Timing pulley
Material	Aluminum
Pitch	8mm 8M
Number of Teeth	44
Pitch Diameter	4.411in
Bore Diameter	1-1/8in
Pulley Type	No hub with flanges
Mounting Type	QD style bushing
For Use With	30mm wide belt
Includes	QD bushing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/A44-8M30-SPBO-1125.pdf>
See store item page for other formats.