

# A6011405-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, unshielded, 5 conductors (includes ground), 14 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6011405-1>

## Technical Specifications

|                             |                                |
|-----------------------------|--------------------------------|
| <b>Brand</b>                | LUTZE                          |
| <b>Item</b>                 | Cable                          |
| <b>Series</b>               | Silflex FBP                    |
| <b>Wire/Cable Type</b>      | Control                        |
| <b>UL Wire/Cable Type</b>   | AWM                            |
| <b>Applicable Standards</b> | UL 20886 and ECOLAB            |
| <b>Application</b>          | Food and beverage              |
| <b>Flexibility</b>          | Flexible                       |
| <b>Voltage Rating</b>       | 1000V                          |
| <b>Conductors</b>           | 5 conductors (includes ground) |
| <b>Conductor Size</b>       | 14 AWG                         |
| <b>Conductor Stranding</b>  | 41-stranded                    |
| <b>Conductor Material</b>   | Bare copper                    |

|                                       |   |
|---------------------------------------|---|
| <b>Conductor Insulation Material</b>  | Polypropylene   |
| <b>Conductor Insulation Color</b>     | Black with white numbers and green/yellow ground  |
| <b>Shielding</b>                      | Unshielded  |
| <b>Jacket Material</b>                | TPE   |
| <b>Jacket Color</b>                   | Black   |
| <b>Nominal Overall Cable Diameter</b> | 0.367in   |
| <b>Bulk Length</b>                    | Cut to length   |
| <b>Package Type</b>                   | <ul style="list-style-type: none"><li>• 20 to 75ft = Coil</li><li>• 76 to 290ft = 14 x 7in Reel</li><li>• 291 to 415ft = 14 x 10in Reel</li><li>• 416 to 500ft = 16 x 10in Reel</li></ul> |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | none  |
| <b>UL Recognized File #</b> | E197090   |
| <b>UL Hazardous File #</b>  | none  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |