

A6011604-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, unshielded, 4 conductors (includes ground), 16 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6011604-1>

Technical Specifications

Brand	LUTZE	Conductor Insulation Material	Polypropylene
Item	Cable	Conductor Insulation Color	Black with white numbers and green/yellow ground
Series	Silflex FBP	Shielding	Unshielded
Wire/Cable Type	Control	Jacket Material	TPE
UL Wire/Cable Type	AWM	Jacket Color	Black
Applicable Standards	UL 20886 and ECOLAB	Nominal Overall Cable Diameter	0.274in
Application	Food and beverage	Bulk Length	Cut to length
Flexibility	Flexible	Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 520ft = 14 x 7in Reel• 521 to 740ft = 14 x 10in Reel• 741 to 1000ft = 16 x 10in Reel
Voltage Rating	1000V		
Conductors	4 conductors (includes ground)		
Conductor Size	16 AWG		
Conductor Stranding	26-stranded		
Conductor Material	Bare copper		

Agency Approvals

UL Listed File #	none
UL Recognized File #	E197090
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement