

# A6011804-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, unshielded, 4 conductors (includes ground), 18 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6011804-1>

## Technical Specifications

|                                      |                                |
|--------------------------------------|--------------------------------|
| <b>Brand</b>                         | LUTZE                          |
| <b>Item</b>                          | Cable                          |
| <b>Series</b>                        | Silflex FBP                    |
| <b>Wire/Cable Type</b>               | Control                        |
| <b>UL Wire/Cable Type</b>            | AWM                            |
| <b>Applicable Standards</b>          | UL 20886                       |
| <b>Application</b>                   | Food and beverage              |
| <b>Flexibility</b>                   | Flexible                       |
| <b>Voltage Rating</b>                | 1000V                          |
| <b>Conductors</b>                    | 4 conductors (includes ground) |
| <b>Conductor Size</b>                | 18 AWG                         |
| <b>Conductor Stranding</b>           | 16-stranded                    |
| <b>Conductor Material</b>            | Bare copper                    |
| <b>Conductor Insulation Material</b> | Polypropylene                  |

|                                       |  |
|---------------------------------------|--|
| <b>Conductor Insulation Color</b>     | Black with white numbers and green/yellow ground   |
| <b>Shielding</b>                      | Unshielded   |
| <b>Jacket Material</b>                | TPE  |
| <b>Jacket Color</b>                   | Black  |
| <b>Nominal Overall Cable Diameter</b> | 0.248in  |
| <b>Bulk Length</b>                    | Cut to length  |
| <b>Package Type</b>                   | 1 to 99ft = Coil, 100 to 630ft = 14 x 7in Reel, 631 to 910ft = 14 x 10in Reel, 911 to 1400ft = 16 x 10in Reel, 1401 to 1980ft = 18 x 10in Reel, 1981 to 2570ft = 18 x 13in Reel, 2571 to 5530ft = 24 x 17in Wooden Reel, 5531 to 9100ft = 30 x 17in Wooden Reel, 9101 to MAX = Large Wooden Reel |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | none  |
| <b>UL Recognized File #</b> | E197090   |
| <b>UL Hazardous File #</b>  | none  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |