

# A6012004-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, unshielded, 4 conductors (includes ground), 20 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6012004-1>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Cable
<b>Series</b>	Silflex FBP
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 20886 and ECOLAB
<b>Application</b>	Food and beverage
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	1000V
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	10-stranded
<b>Conductor Material</b>	Bare copper

<b>Conductor Insulation Material</b>	Polypropylene
<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground
<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.219in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 20 to 99ft = Coil</li><li>• 100 to 815ft =14 x 7in Reel</li><li>• 816 to 1000ft =14 x 10in Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	none
<b>UL Recognized File #</b>	E197090
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>