

A6012007-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, unshielded, 7 conductors (includes ground), 20 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6012007-1>

Technical Specifications

| | |
|-----------------------------|--------------------------------|
| Brand | LUTZE |
| Item | Cable |
| Series | Silflex FBP |
| Wire/Cable Type | Control |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 20886 and ECOLAB |
| Application | Food and beverage |
| Flexibility | Flexible |
| Voltage Rating | 1000V |
| Conductors | 7 conductors (includes ground) |
| Conductor Size | 20 AWG |
| Conductor Stranding | 10-stranded |
| Conductor Material | Bare copper |

| | |
|---------------------------------------|---|
| Conductor Insulation Material | Polypropylene |
| Conductor Insulation Color | Black with white numbers and green/yellow ground |
| Shielding | Unshielded |
| Jacket Material | TPE |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.255in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 600ft = 14 x 7in Reel• 601 to 855ft = 14 x 10in Reel• 856 to 1000ft = 16 x 10in Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | none |
| UL Recognized File # | E197090 |
| UL Hazardous File # | none |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |