

# A6021804-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, shielded, 4 conductors (includes ground), 18 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6021804-1>

## Technical Specifications

Brand	LUTZE	Conductor Insulation Material	Polypropylene
Item	Cable	Conductor Insulation Color	Black with white numbers and green/yellow ground
Series	Silflex FBP	Shielding	Shielded
Wire/Cable Type	Control	Jacket Material	TPE
UL Wire/Cable Type	AWM	Jacket Color	Black
Applicable Standards	UL 20886 and ECOLAB	Nominal Overall Cable Diameter	0.289in
Application	Food and beverage	Bulk Length	Cut to length
Flexibility	Flexible	Package Type	<ul style="list-style-type: none"><li>• 20 to 99ft = Coil</li><li>• 100 to 465ft =14 x 7in Reel</li><li>• 466 to 500ft =14 x 10in Reel</li></ul>
Voltage Rating	1000V		
Conductors	4 conductors (includes ground)		
Conductor Size	18 AWG		
Conductor Stranding	16-stranded		
Conductor Material	Bare copper		

## Agency Approvals

UL Listed File #	none
UL Recognized File #	E197090
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>