

A6021818-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, shielded, 18 conductors (includes ground), 18 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6021818-1>

Technical Specifications

Brand	LUTZE
Item	Cable
Series	Silflex FBP
Wire/Cable Type	Control
UL Wire/Cable Type	AWM
Applicable Standards	UL 20886
Application	Food and beverage
Flexibility	Flexible
Voltage Rating	1000V
Conductors	18 conductors (includes ground)
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	Polypropylene

Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Shielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.489in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 165ft = 14 x 7in Reel, 166 to 235ft = 14 x 10in Reel, 236 to 355ft = 16 x 10in Reel, 356 to 500ft = 18 x 10in Reel, 501 to 650ft = 18 x 13in Reel, 651 to 1450ft = 24 x 17in Wooden Reel, 1451 to 2325ft = 30 x 17in Wooden Reel, 2326 to to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E197090
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement