

A6021825-1 Cut Sheet



LUTZE Silflex FBP flexible control cable, shielded, 25 conductors (includes ground), 18 AWG, bare copper, polypropylene conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A6021825-1>

Technical Specifications

| | |
|--------------------------------------|---------------------------------|
| Brand | LUTZE |
| Item | Cable |
| Series | Silflex FBP |
| Wire/Cable Type | Control |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 20886 |
| Application | Food and beverage |
| Flexibility | Flexible |
| Voltage Rating | 1000V |
| Conductors | 25 conductors (includes ground) |
| Conductor Size | 18 AWG |
| Conductor Stranding | 16-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | Polypropylene |

| | |
|---------------------------------------|---|
| Conductor Insulation Color | Black with white numbers and green/yellow ground |
| Shielding | Shielded |
| Jacket Material | TPE |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.569in |
| Bulk Length | Cut to length |
| Package Type | 1 to 50ft = Coil, 51 to 120ft = 14 x 7in Reel, 121 to 170ft = 14 x 10in Reel, 171 to 260ft = 16 x 10in Reel, 261 to 370ft = 18 x 10in Reel, 371 to 480ft = 18 x 13in Reel, 481 to 1050ft = 24 x 17in Wooden Reel, 1051 to 1730ft = 30 x 17in Wooden Reel, 1731 to MAX = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | E197090 |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |