

A61201 Cut Sheet



LUTZE HAR H07V-K hook-up wire, single conductor, 12 AWG (4mm²), 56-stranded, tinned copper, PVC conductor insulation material, black, 450/750V (H07V2-K), 600V (MTW), 328ft carton.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A61201>

Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | LUTZE |
| Item | Wire |
| Wire/Cable Type | HAR H07V-K |
| UL Wire/Cable Type | AWM, MTW and HAR |
| Applicable Standards | UL 1015, UL 1063 and UL 1581 |
| Application | Hook-up |
| Flexibility | Flexible |
| Voltage Rating | 450/750V (H07V2-K), 600V (MTW) |
| Conductors | Single conductor |
| Conductor Size | 12 AWG (4mm ²) |
| Conductor Stranding | 56-stranded |
| Conductor Material | Tinned copper |
| Conductor Insulation Material | PVC |
| Conductor Insulation Color | Black |
| Bulk Length | 328ft carton |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E220830 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LL77660 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |