


# A61800 Cut Sheet



LUTZE HAR H05V-K hook-up wire, single conductor, 18 AWG (1.0mm<sup>2</sup>), 32-stranded, tinned copper, PVC conductor insulation material, green/yellow, 300/500V (H05V2-K), 600V (MTW), 328ft carton.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A61800>

## Technical Specifications

<b>Brand</b>	LUTZE
<b>Item</b>	Wire
<b>Wire/Cable Type</b>	HAR H05V-K
<b>UL Wire/Cable Type</b>	AWM, MTW and HAR
<b>Applicable Standards</b>	UL 1015, UL 1063 and UL 1581
<b>Application</b>	Hook-up
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	300/500V (H05V2-K), 600V (MTW)
<b>Conductors</b>	Single conductor
<b>Conductor Size</b>	18 AWG (1.0mm <sup>2</sup> )
<b>Conductor Stranding</b>	32-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Green/yellow
<b>Bulk Length</b>	328ft carton

## Agency Approvals

<b>UL Listed File #</b>	E220830
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LL77660
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>