

A774 Cut Sheet



Marathon incremental (quadrature) rotary encoder kit, 5-26 VDC, line driver (differential) output, 1024 ppr, IP67. For use with Marathon Blue Max TEFC encoder motors. Mounting hardware included. Dynapar HS35 encoder.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/A774>

Technical Specifications

Brand	Marathon
Item	Encoder kit
Feedback Type	Incremental (quadrature)
Encoder Type	Rotary
Replacement	No
Duty Rating	Heavy-duty
Voltage Rating	5-26 VDC
Encoder Output Type	Line driver (differential)
Encoder Resolution	1024 ppr
Shaft Type	Hollow
Shaft Diameter	1in
Flange Mount	No
Encoder Body Diameter	3-3/4in
IP Rating	IP67
Connector Type	10-pin Military Style (MS) connector
For Use With	Marathon Blue Max TEFC encoder motors
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document