

AAM2T93Z11 Cut Sheet



AutomationDirect IEC limit switch, 360 degree stainless steel spring, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AAM2T93Z11>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	IEC
Actuator Type	360 degree stainless steel spring
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	30.3mm
Mounting Hole Spacing	20-22mm
Material	Zinc alloy
IP Rating	IP66
Operating Temperature	-10 to 70 deg C
Connection	1/2in NPT cable entry

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document